数据信息页

U-LINK-EC-50-WM-DEVICES-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

应用举例



The Weidmüller u-link Remote Access Service in easyConnect offers an easy way to securely access Ethernet devices in remote networks.
With the u-link VPN Server as the central meeting point server, the VPN clients (service PC, Weidmüller u-link client devices and Third-Party OpenVPN capable devices) always connect outbound and thus conform to typical IT security requirements.
Separate database and server instances are used for each customer account (secure client isolation) to ensure data integrity.
Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected OpenVPN connection.
The u-link principle is "configuration instead of programming". The use is intuitive and does not require expert knowledge.
Featureset:

- 1-click VPN remote access for service PCs
- Web Access: web connections to remote hosts fully browser-based for use with tablets or smartphones
- Organization and Group Management
- Topologies including third-party end devices
- Firmware management: display of the firmware status of all Weidmüller devices and the option of time-controlled, automated firmware updates
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: overview of activities with comprehensive filter and export functions

With u-link Remote Access integrated into easyConnect, Weidmüller offers a scalable licensing concept based on the number and type of connected devices as well as the required number of simultaneous VPN connections.
Weidmüller device licenses:

- Available for up to 50, 100, 250, 500, 750 or 1000 Weidmüller devices
- Provides secure remote access to the corresponding number of Weidmüller devices through easyConnect
- License validity: 1 year

Third-party devices via OpenVPN:

- Available for up to 600, 1200 or 1800 third-party devices
- Enables the integration of devices from other manufacturers that support OpenVPN
- Allows Weidmüller and compatible third-party devices to be centrally accessed through the same easyConnect environment
- License validity: 1 year

Additional simultaneous VPN connections:

- Available for 1, 5 or 10 additional simultaneous connections
- Increases the number of parallel remote access sessions within the easyConnect instance
- Suitable for additional users or parallel service activities
- License validity: 1 year

U-LINK-EC-50-WM-DEVICES-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Remote access to and from China:
- Dedicated license for devices or service PCs located in China
- Uses the dedicated easyConnect infrastructure provided for China
- License validity: 1 year

Trial license:
A 90-day trial license is available for testing u-link Remote Access in easyConnect. The trial license includes up to 50 devices, up to 50 users and 1 simultaneous VPN connection. The trial license is not available as a separate eShop product and can only be activated directly within easyConnect. The modular licensing concept allows u-link Remote Access in easyConnect to be scaled according to the number of connected devices and required parallel remote access sessions.

通用订货数据

版本	License code for u-link Remote Access Service.
订货号	3227450000
类型	U-LINK-EC-50-WM-DEVICES-1Y
数量	ST

数据信息页

U-LINK-EC-50-WM-DEVICES-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技术数据

尺寸和重量

净重	0 g

温度

存储温度		工作温度	

功能和特征

固件管理	显示所有 u-link 客户端的固件版本和可选的、时间控制的自动固件更新（针对选定的设备类别）	双因素认证类型	E-mail
系统可用性	≥ 99.6%	可同时使用的贯通 VPN 连接	1 (可以通过预订更多的贯通 VPN 连接进行扩展)
每月数据流量和带宽	不限（以正常市场使用为准）	用户组织	将服务用户以分组形式组织，将选择性访问权限分配至设备拓扑布局，根据分组来分配同设备配置以及用户管理相关的权限，组织权限框架下的组织自我管理
可配置用户对象的数量 (服务计算机)	无限制	使用信息	扩展报告和统计信息（连接报告，使用持续时间，数据流量）
VPN 通道带宽	100 Mbit/s	设备管理	设备基础结构插图 (远程接入对象) 通过位置，分组和设备对象以清晰的树状结构显示
周期	自许可证密钥激活或现有许可证到期之日起 1 年。在激活过程中可以看到单独的许可条款。	基于网络的访问类型 (easyAccess)	本地网络服务器
魏德米勒硬件上可配置的 u-link 客户端数量（远程网络接入点）	50		

系统要求

硬件，远程目标网络	魏德米勒硬件，带 u-link VPN 客户端	硬件 (服务计算机)	装有 Windows 10 或 11 操作系统的电脑
门户管理（用户/设备配置）	通过网络浏览器 (HTTPS)，通过用户名和密码登录	VPN 软件 (服务计算机)	u-link VPN-client (installation on PC)

其他各类

激活	账户管理员在 easyConnect 门户中输入许可证密钥（功能即刻生效）。	发货时已含附件	带有许可证密钥的电子邮件

分类

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		