
数据信息页

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

产品图片





通用订货数据

版本	, 插座, THT/THR 焊接联接, 90°, Tube
订货号	8000166085
类型	MHS 6/04-3PM/04 H M4 T3 B T
数量	
产品数据	IEC: 1000 V UL:
包装	Tube

数据信息页

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技术数据

尺寸和重量

深	25 mm	深度 (英寸)	0.9842 inch
高度	16.6 mm	高度 (英寸)	0.6535 inch
最低安装高度	13.4 mm	宽度	41.625 mm
宽度 (英寸)	1.6388 inch		

温度

环境温度	-50 °C...120 °C

材料数据

绝缘材料	PA 9T	颜色编码	黑色
比色表 (相似)	RAL 9011	Moisture Level (MSL)	1
阻燃等级符合 UL 94	V-0	插针材料	CuMg
触点材料	铜合金	插针镀层	镀锡
最低存放温度.	-40 °C	最高存放温度	70 °C
最低操作温度	-50 °C	最高操作温度	125 °C

额定数据符合 IEC 标准

额定电压，用于过电压等级（污染等级 II/2）	1000 V	额定电压，用于过电压等级（污染等级 III/2）	160 V
额定电压，用于过电压等级（污染等级 III/3）	160 V		

重要注意事项

备注	• Rated current related to rated cross-section & min. No. of poles. • P on drawing = pitch • Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. • Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

分类

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-03-01
ECLASS 15.0	27-46-03-01		

数据信息页

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

图纸

产品图片

