

DC SB M 50A 4POL CG 1KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Všeobecné objednáací údaje**

| | |
|------------------|--|
| Verze | Fotovoltaika, Přepínač, Spínací odpojovač, 1000 V, DC verze, 50 A, pól 4, Ruční spínač |
| Číslo objednávky | 3123800000 |
| Typ | DC SB M 50A 4POL CG 1KV |
| GTIN (EAN) | 4099987272018 |
| Množství | 1 items |

DC SB M 50A 4POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Osvědčení

ROHS Shoda

Rozměry a hmotnosti

| | | | |
|----------------|----------|---------------------|-------------|
| Hloubka | 121.5 mm | Hloubka (v palcích) | 4.7835 inch |
| Výška | 165 mm | Výška (v palcích) | 6.4961 inch |
| Šířka | 140 mm | Šířka (v palcích) | 5.5118 inch |
| Čistá hmotnost | 644 g | | |

Teploty

Okolní teplota -30 °C...50 °C

Shoda produktu s prostředím

Stav souladu se směrnici RoHS V souladu bez výjimky
REACH SVHC Ne SVHC nad 0,1 wt%

Součást dodávky

| | | |
|------------------------|----------|------------------------|
| Zahrnutá příslušenství | Odstavec | Vidlicová kabelová oka |
| | Množství | 8 |

Obecná data

Stupeň krytí IP65

Klasifikace

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000216 | ETIM 9.0 | EC004830 |
| ETIM 10.0 | EC004830 | ECLASS 14.0 | 27-07-02-03 |
| ECLASS 15.0 | 27-07-02-03 | | |

Listy specifikací zakázky

| | |
|--------------------|---|
| Dlouhá specifikace | <p>Load break switch in polyester housing. Suitable for switching off the DC side. Number of poles: 4 Operating current, rated value (Ie): - according to IEC (PV1, 1000 V): 50 A - according to IEC (PV1, 1500 V): 20 A - according to IEC (PV2, 1000 V): 20 A - according to IEC (PV2, 1500 V): 8 A Rated insulation voltage (Ui): - according to IEC: 1500 V Suitability for use: Main switch: Yes Number of contacts normally open: 4</p> |
|--------------------|---|

DC SB M 50A 4POL CG 1KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Number of contacts normally closed: 0
Number of switching positions: 2
Lockable: Yes
The switch is mounted using 4 screws.
Protection class (IP): 65
Polyester housing with M25 cable Gland with multiple sealing inserts for PV conductor with max. conductor cross-section: 6 mm².
Dimensions HxWxD: 165x140x121.5 mm.
Approval according to low voltage switchgear and controlgear IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)

DC SB M 50A 4POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

