
Data sheet

# EGT2 EG2/EN SCHALT.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product is no longer available, Data sheet for information only




The profiles of the switch and button components match those of the electronic components.
Switches and buttons facilitate commissioning, servicing, monitoring and repair of industrial installations.

## General ordering data

| | |
|---|---|
| Version | , Function component CO contact, switching, Screw connection |
| Order No. | 0104060000 |
| Type | EGT2 EG2/EN SCHALT. |
| GTIN (EAN) | 4008190119713 |
| Qty. | 10 items |
| Delivery status | Discontinued |
| Available until | 2024-10-22T00:00:00+02:00 |

# EGT2 EG2/EN SCHALT.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Height | 50 mm | Height (inches) | 1.9685 inch |
| Width | 18 mm | Width (inches) | 0.7087 inch |
| Length | 58 mm | Length (inches) | 2.2835 inch |
| Net weight | 36.7 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -40 °C...100 °C | Operating temperature | -25 °C...85 |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General data

| | |
|---|---|
| Mounting rail | TS 32, TS 35 |

### Output

| | | | |
|---|---|---|---|
| Rated switching voltage | 250 V AC | AC switching capacity (resistive), max. | 1500 VA @ 250 V |
| AC switching capacity, max. | 1500 VA | Switching capacity | 250 V |
| DC switching capacity (resistive), max. | 180 W @ 30 V | DC switching capacity, max. | 180 W |
| Switching capacity | 30 V | | |

### General data

| | | | |
|---|---|---|---|
| Mounting rail | TS 32, TS 35 | Colour | beige |

### Connection data

| | | | |
|---|---|---|---|
| Wire connection method | Screw connection | Clamping range, rated connection | 6 mm² |
| Clamping range, min. | 0.5 mm² | Clamping range, max. | 6 mm² |
| Wire connection cross section, finely stranded, max. | 4 mm² | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC002498 | ETIM 9.0 | EC002498 |
| ETIM 10.0 | EC002498 | ECLASS 14.0 | 27-37-13-92 |
| ECLASS 15.0 | 27-37-13-92 | | |

# EGT2 EG2/EN SCHALT.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Steel




Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

| | | |
|---|---|---|
| Type | TS 32X15 2M/ST/ZN | Version |
| Order No. | 0122800000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, |
| GTIN (EAN) | 4008190066307 | Width: 2000 mm, Height: 33 mm, Depth: 15 mm |
| Qty. | 20 M | |

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

| | | |
|---|---|---|
| Type | EWK 2 | Version |
| Order No. | 0199360000 | End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C |
| GTIN (EAN) | 4008190023546 | |
| Qty. | 50 ST | |

### Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

| | | |
|---|---|---|
| Type | TS 35X7.5 2M/ST/ZN | Version |
| Order No. | 0383400000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, |
| GTIN (EAN) | 4008190088026 | Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm |
| Qty. | 40 M | |


# EGT2 EG2/EN SCHALT.

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

| | | |
|---|---|---|
| Type | EW 35 | Version |
| Order No. | 0383560000 | End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C |
| GTIN (EAN) | 4008190181314 | |
| Qty. | 50 ST | |

### Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

| | | |
|---|---|---|
| Type | TS 35X15/2.3 2M/ST/ZN | Version |
| Order No. | 0498000000 | Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, |
| GTIN (EAN) | 4008190042493 | Width: 2000 mm, Height: 35 mm, Depth: 15 mm |
| Qty. | 20 M | |