


## EGT5 EG2/EN TASTER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Product is no longer available, Data sheet for information only



The profiles of the switch and button components match those of the electronic components.  
 Switches and buttons facilitate commissioning, servicing, monitoring and repair of industrial installations.

### General ordering data

Version	, Function component CO contact, off position in the middle, sensing on both sides, Screw connection
Order No.	<a href="#">0104260000</a>
Type	EGT5 EG2/EN TASTER
GTIN (EAN)	4008190100247
Qty.	10 items
Delivery status	Discontinued
Available until	2024-10-22T00:00:00+02:00

## EGT5 EG2/EN TASTER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Height	50 mm	Height (inches)	1.9685 inch
Width	18 mm	Width (inches)	0.7087 inch
Length	58 mm	Length (inches)	2.2835 inch
Net weight	41.9 g		

### Temperatures

Storage temperature	-40 °C...100 °C	Operating temperature	-25 °C...85 °C
---------------------	-----------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Mounting rail	TS 32, TS 35
---------------	--------------

### Output

Rated switching voltage	250 V AC	AC switching capacity (resistive), max.	1500 VA @ 250 V
AC switching capacity, max.	1500 VA	Switching capacity	250 V
DC switching capacity (resistive), max.	180 W @ 30 V	DC switching capacity, max.	180 W
Switching capacity	30 V		

### General data

Mounting rail	TS 32, TS 35	Colour	beige
---------------	--------------	--------	-------

### Connection data

Wire connection method	Screw connection	Clamping range, rated connection	6 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	6 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC002498	ETIM 9.0	EC002498
ETIM 10.0	EC002498	ECLASS 14.0	27-37-13-92
ECLASS 15.0	27-37-13-92		

## EGT5 EG2/EN TASTER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Steel




Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

Type	TS 32X15 2M/ST/ZN	Version	
Order No.	<a href="#">0122800000</a>	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,	
GTIN (EAN)	4008190066307	Width: 2000 mm, Height: 33 mm, Depth: 15 mm	
Qty.	20 M		

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

Type	EWK 2	Version	
Order No.	<a href="#">0199360000</a>	End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C	
GTIN (EAN)	4008190023546		
Qty.	50 ST		

### Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

Type	TS 35X7.5 2M/ST/ZN	Version	
Order No.	<a href="#">0383400000</a>	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,	
GTIN (EAN)	4008190088026	Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm	
Qty.	40 M		

## EGT5 EG2/EN TASTER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

Type	EW 35	Version	
Order No.	<a href="#">0383560000</a>	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C	
GTIN (EAN)	4008190181314		
Qty.	50 ST		

### Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

### General ordering data

Type	TS 35X15/2.3 2M/ST/ZN	Version	
Order No.	<a href="#">0498000000</a>	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,	
GTIN (EAN)	4008190042493	Width: 2000 mm, Height: 35 mm, Depth: 15 mm	
Qty.	20 M		