

**AP SAK4-10 I****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

**General ordering data**

|            |  |
|------------|--|
| Version    | End plate for terminals, black, Height: 40 mm, Width: 1.5 mm, V-2, PA 66, Snap-on: Yes |
| Order No.  | <a href="#">0117910000</a>   |
| Type       | AP SAK4-10 I   |
| GTIN (EAN) | 4008190183707  |
| Qty.       | 20 items   |

**AP SAK4-10 I**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 36 mm  | Depth (inches)  | 1.4173 inch |
| Height     | 40 mm  | Height (inches) | 1.5748 inch |
| Width      | 1.5 mm | Width (inches)  | 0.0591 inch |
| Net weight | 2.86 g |                 |             |

**Temperatures**

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C         |

**Environmental Product Compliance**

|                          |                             |                 |  |
|--------------------------|-----------------------------|-----------------|--|
| RoHS Compliance Status   | Compliant without exemption |                 |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                 |  |
| Product Carbon Footprint | Cradle to gate              | 0.024 kg CO2eq. |  |

**Material data**

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Basic material            | PA 66 | Colour | black |
| UL 94 flammability rating | V-2   |        |       |

**System specifications**

Version End plate

**Additional technical data**

Snap-on Yes Installation advice Direct mounting

**General**

Installation advice Direct mounting

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |