



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

### General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 99 A, Number of poles: 4, Pitch in mm (P): 8.00, Insulated: No, Width: 63.8 mm
Order No.	<a href="#">0123800000</a>
Type	QL 4 SAK35
GTIN (EAN)	4008190165390
Qty.	20 items

## QL 4 SAK35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	8 mm	Height (inches)	0.315 inch
Width	63.8 mm	Width (inches)	2.5118 inch
Net weight	11.3 g		

## Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## Material data

Basic material Cu Zn Colour grey

## System specifications

Version for cross-connection link

## Additional technical data

Type of fixing when screwed in Installation advice Direct mounting  
Explosion-tested version No

## Dimensions

Pitch in mm (P) 8.00 mm

## General

Number of poles 4 Installation advice Direct mounting

## Rating data

Nominal current 99 A

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		