

STB 16/D7/4/M4 SAK35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	SAK Series, Socket
Order No.	0140200000
Type	STB 16/D7/4/M4 SAK35
GTIN (EAN)	4008190134884
Qty.	50 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 3.5 g

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material Copper - zinc Surface finish galvanized
 Colour grey

System specifications

Version For the terminals

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
 Explosion-tested version No

Dimensions

O.D. 7 mm Plug-in depth 14 mm

General

Installation advice Direct mounting Surface finish galvanized

Classifications

ETIM 8.0 EC002848 ETIM 9.0 EC002848
 ETIM 10.0 EC002848 ECLASS 14.0 27-25-03-90
 ECLASS 15.0 27-25-03-90