
Data sheet

QL 3 SAK70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 180 A, Number of poles: 3, Pitch in mm (P): 14.00, Insulated: No, Width: 58 mm
Order No.	0167000000
Type	QL 3 SAK70
GTIN (EAN)	4008190001018
Qty.	5 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-06-30T00:00:00+02:00

Data sheet

QL 3 SAK70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	14 mm	Height (inches)	0.5512 inch
Width	58 mm	Width (inches)	2.2835 inch
Net weight	25.2 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	86596b21-b817-43a9-8e4c-ac00e41b9a24

Material data

Basic material	Cu Zn	Colour	grey

System specifications

Version	for cross-connection link

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	14.00 mm

General

Number of poles	3	Installation advice	Direct mounting

Rating data

Nominal current	180 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		