

STB 14/D5/2.3/M3 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	SAK Series, Socket
Order No.	0168600000
Type	STB 14/D5/2.3/M3 SAK2.5
GTIN (EAN)	4008190135225
Qty.	50 items

STB 14/D5/2.3/M3 SAK2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Diameter	5 mm	Net weight	2.01 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	Copper - zinc	Surface finish	galvanized
Colour	grey		

System specifications

Version For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

O.D.	5 mm	Diameter	5 mm
Plug-in depth	12.5 mm		

General

Installation advice	Direct mounting	Surface finish	galvanized
---------------------	-----------------	----------------	------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		