



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

### General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 12 mm, No
Order No.	<a href="#">0186100000</a>
Type	H2,5/12
GTIN (EAN)	4008190172954
Qty.	1000 items
Packaging	loose

## H2,5/12

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

### Dimensions and weights

Net weight 0.11 g

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

### Wire-end ferrules

Contact surface diameter (D1)	2.2 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	3.4 mm	L1 in mm	12.00 mm
Wire connection cross section AWG, max.	AWG 14	Stripping length	12 mm
Conductor cross-section	2.5 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

