

**EWK 2****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

Version	End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C
Order No.	<a href="#">0199360000</a>
Type	EWK 2
GTIN (EAN)	4008 190023546
Qty.	50 items

## EWK 2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	42 mm	Depth (inches)	1.6535 inch
Height	27 mm	Height (inches)	1.063 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	7.12 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	beige
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals	Mounting rail	TS 32
---------	-------------------	---------------	-------

### Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
Locking	for screw fixing		

### Conductors for clamping (rated connection)

Tightening torque, max.	1 Nm	Tightening torque, min.	0.5 Nm
-------------------------	------	-------------------------	--------

### General

Installation advice	Direct mounting	Mounting rail	TS 32
---------------------	-----------------	---------------	-------

### Classifications

ETIM 8.0	EC001041	ETIM 9.0	EC001041
ETIM 10.0	EC001041	ECLASS 14.0	27-25-03-02
ECLASS 15.0	27-25-03-02		