


EP 2 SAKG46/32 HP/TF/GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Version	End and partition plate for terminals, yellow, Height: 160 mm, Width: 2 mm, V-2, PA 66
Order No.	0205400000
Type	EP 2 SAKG46/32 HP/TF/GE
GTIN (EAN)	4008190027223
Qty.	10 items

EP 2 SAKG46/32 HP/TF/GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	90.5 mm	Depth (inches)	3.563 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	2 mm	Width (inches)	0.0787 inch
Net weight	35.7 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	8689236b-1c04-4b82-9d8d-177abb5f9950

Material data

Basic material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Snap-on	No
---------	----

Dimensions

TS 32 offset	80 mm
--------------	-------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 9.0	27-14-11-33
ECLASS 9.1	27-14-11-33	ECLASS 10.0	27-14-11-33
ECLASS 11.0	27-14-11-33	ECLASS 12.0	27-14-11-33
ECLASS 13.0	27-25-03-01	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		