

**CLI C 2-4 GE/SW B MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                     |
|------------|---------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No.  | <a href="#">0251311639</a>                                          |
| Type       | CLI C 2-4 GE/SW B MP                                                |
| GTIN (EAN) | 4008190010058                                                       |
| Qty.       | 100 items                                                           |

## CLI C 2-4 GE/SW B MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch  |
| Height     | 4 mm   | Height (inches) | 0.1575 inch |
| Width      | 7 mm   | Width (inches)  | 0.2756 inch |
| Net weight | 0.16 g |                 |             |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                              |                                                |                |
|----------------------------------------------|------------------------------------------------|----------------|
| Material colour according to resistance code | 4                                              |                |
| Orientation of print                         | horizontal                                     |                |
| Type of printing                             | Standard                                       |                |
| Printing method                              | hot-embossing                                  |                |
| Version                                      | MultiPack                                      |                |
| Width                                        | 7 mm                                           |                |
| UL 94 flammability rating                    | V-0                                            |                |
| Operating temperature range, max.            | 80 °C                                          |                |
| Operating temperature range, min.            | -30 °C                                         |                |
| Colour                                       | yellow                                         |                |
| Halogen                                      | Yes                                            |                |
| Insulation cross-section, max.               | 10                                             |                |
| Basic material                               | PVC, soft, without Cadmium                     |                |
| Colour of printing                           | black                                          |                |
| Printed characters                           | Upper-case letters                             |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Recommended industries                       | Process, Machinery                             |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Operating temperature range                  | -30...80 °C                                    |                |
| Imprint                                      | B                                              |                |

## Conductor and cable markers

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                      | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min.    | 2.5 mm <sup>2</sup>      | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.             | 4 mm                     | Conductor O.D.                | 4 - 10 mm          |
| Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |                               |                    |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration