

**Product image**

In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

**General ordering data**

Version	Cross-connector (terminal), Plugged, beige, 44 A, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: Yes, Width: 12 mm
Order No.	<a href="#">0270760000</a>
Type	QS 2/12/4
GTIN (EAN)	4008190011420
Qty.	20 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	34.5 mm	Depth (inches)	1.3583 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	12 mm	Width (inches)	0.4724 inch
Net weight	7 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	20993c56-321a-4ec1-8646-b7d545a927f2

### Material data

Basic material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	12.00 mm
-----------------	----------

### General

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

### Rating data

Rated voltage	400 V	Nominal current	44 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		