

**STB 25 IH/GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

STB 25 IH/6N 027120

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 13 mm, Depth: 30.5 mm
Order No.	<a href="#">0271200000</a>
Type	STB 25 IH/GN
GTIN (EAN)	4008190155889
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00
Alternative product	<a href="#">STB 2.1.6/IH/GN WTL6/3</a>

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	30.5 mm	Depth (inches)	1.2008 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Diameter	7.2 mm	Net weight	4.18 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea		

**Material data**

Basic material	PA 66	Colour	green
UL 94 flammability rating	V-2		

**System specifications**

Version	For the mounting rails
---------	------------------------

**Additional technical data**

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

**Dimensions**

Diameter	7.2 mm	Plug-in depth	13 mm
----------	--------	---------------	-------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		