

STB 25 IH/SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Socket (terminal), Plug-in depth: 13 mm, Depth: 30 mm
Order No.	0271500000
Type	STB 25 IH/SW
GTIN (EAN)	4008190030162
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00
Alternative product	STB 2.1.6/IH/SW WTL6/3

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Net weight	4.26 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	PA 66	Colour	black
UL 94 flammability rating	V-2		

System specifications

Version For the mounting rails

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

Dimensions

Plug-in depth 13 mm

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		