


EP 2/BW SAKG46/32 HP/DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

Version	SAK Series, End plate, dark beige, 75.5 mm
Order No.	0271900000
Type	EP 2/BW SAKG46/32 HP/DB
GTIN (EAN)	4008190172497
Qty.	10 items
Delivery status	Discontinued
Available until	2024-04-30T00:00:00+02:00

EP 2/BW SAKG46/32 HP/DB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	90.5 mm	Depth (inches)	3.563 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	75.5 mm	Width (inches)	2.9724 inch
Net weight	51.2 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	8689236b-1c04-4b82-9d8d-177abb5f9950

Material data

Basic material	Plastic	Colour	dark beige
UL 94 flammability rating	V-2		

System specifications

Version	with end bracket
---------	------------------

Additional technical data

Snap-on	Yes	Type of fixing	when screwed in
Explosion-tested version	No	Locking	for screw fixing

Dimensions

Pitch in mm (P)	160.00 mm	TS 32 offset	80 mm
-----------------	-----------	--------------	-------

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		