


**DKSUE NSCH/ESCH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Fastening element (Terminal), silver, Height: 12.5 mm, Width: 10 mm, Steel, 180 °C
Order No.	<a href="#">028010000</a>
Type	DKSUE NSCH/ESCH
GTIN (EAN)	4008190036348
Qty.	100 items

**DKSUE NSCH/ESCH**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	7.7 mm	Depth (inches)	0.3031 inch
Height	12.5 mm	Height (inches)	0.4921 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	1.31 g		

**Temperatures**

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	180 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Steel	Colour	silver
----------------	-------	--------	--------

**System specifications**

Version	Miscellaneous
---------	---------------

**Additional technical data**

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

**Dimensions**

Pitch in mm (P)	13.50 mm
-----------------	----------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		