


**NSCH 1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

With our bus bars in various materials and the associated accessories, you can connect cables in the smallest installation space. Depending on the application, potentials can be collected, distributed or dissipated.

**General ordering data**

Version	Busbar (terminal), Natural, Height: 15 mm, Depth: 2 mm, Copper
Order No.	<a href="#">028020000</a>
Type	NSCH 1M
GTIN (EAN)	4008190012953
Qty.	10 M

## NSCH 1M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	198.26 g		

## Temperatures

Ambient temperature -5 °C...40 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## Material data

Basic material Copper Surface finish untreated  
 Colour Natural

## Rating data IECEX/ATEX

Certificate No. (IECEX) IECEXULD13.0005U Wire cross section max. (IECEX) 2.5 mm<sup>2</sup>

## Additional technical data

Installation advice Direct mounting

## Conductors for clamping (rated connection)

Type of connection Screw connection

## Dimensions

TS 35 offset 39 mm

## General

Installation advice Direct mounting Surface finish untreated

## Rating data

Nominal current 24 A

## Classifications

ETIM 8.0 EC002848 ETIM 9.0 EC002848  
 ETIM 10.0 EC002848 ECLASS 14.0 27-14-11-92

Creation date 17.02.2026 08:27:08 MEZ

Catalogue status / Drawings

**NSCH 1M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Technical data**

[www.weidmueller.com](http://www.weidmueller.com)

---

ECLASS 15.0

27-14-11-92

---