

H0,5/6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 6 mm, 6 mm, No
Order No.	0282600000
Type	H0,5/6
GTIN (EAN)	4008190184025
Qty.	1000 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

Dimensions and weights

Net weight 0.03 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	1 mm	Contact surface length (L2)	6 mm
Collar diameter (D2)	2.1 mm	L1 in mm	6.00 mm
Wire connection cross section AWG, max.	AWG 20	Stripping length	6 mm
Conductor cross-section	0.5 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawings

