

BFSC M3X25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Mounting screw (Terminal), 3.00 mm, Steel, Depth: 4.8 mm, Width: 4.8 mm, Height: 25 mm
Order No.	0292500000
Type	BFSC M3X25
GTIN (EAN)	4008190177027
Qty.	100 items

BFSC M3X25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	4.8 mm	Width (inches)	0.189 inch
Diameter	3 mm	Net weight	1.38 g

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Steel Colour silver

System specifications

Version for cross-connection link

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
 Explosion-tested version No Type of mounting when screwed in

Dimensions

Diameter 3 mm Metric size of the thread, external 3.00 mm

General

Installation advice Direct mounting

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		