

**TS 32X15 2M/CRN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Stainless steel is a collective term for all types of steel (alloys) with a high degree of purity and corrosion resistance.

**General ordering data**

|            |                                                                                                                 |
|------------|-----------------------------------------------------------------------------------------------------------------|
| Version    | Terminal rail, Accessories, Stainless steel, rust-proof, untreated, Width: 2000 mm, Height: 33 mm, Depth: 15 mm |
| Order No.  | <a href="#">0293220000</a>                                                                                      |
| Type       | TS 32X15 2M/CRN                                                                                                 |
| GTIN (EAN) | 4032248014026                                                                                                   |
| Qty.       | 20 M                                                                                                            |

## TS 32X15 2M/CRN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 15 mm    | Depth (inches)  | 0.5906 inch |
| Height     | 33 mm    | Height (inches) | 1.2992 inch |
| Width      | 2000 mm  | Width (inches)  | 78.74 inch  |
| Net weight | 612.33 g |                 |             |

## Temperatures

|                     |               |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Mounting rail

|                                    |                             |         |
|------------------------------------|-----------------------------|---------|
| Installation advice                | Direct mounting             |         |
| Standards                          | DIN EN 60715                |         |
| Surface finish                     | untreated                   |         |
| Thickness                          | 1.50 mm                     |         |
| Basic material                     | Stainless steel, rust-proof |         |
| Length of the terminal rail        | min.                        | 0 mm    |
|                                    | nominal                     | 2000 mm |
|                                    | max.                        | 2000 mm |
| Pre-punched mounting rail          | No                          |         |
| Slit width                         |                             |         |
| Spacing of holes, centre-to-centre | 0 mm                        |         |
| Slit gap                           |                             |         |
| Slit length                        |                             |         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ETIM 10.0   | EC001285    | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 |             |             |

**Drawings**

