

VP 13,5-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, PG 13.5, 6 mm, Brass, nickel-plated
Order No.	0294900000
Type	VP 13,5-MS65
GTIN (EAN)	4008 190053383
Qty.	100 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00
Alternative product	VP 13,5-K54

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	9 mm	Height (inches)	0.3543 inch
Length	9 mm	Length (inches)	0.3543 inch
Diameter	24 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	5 mm	Net weight	8.58 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

General information

Head diameter	24.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Protection degree	IP68 - 5 bar (30 min.)	Cable gland	PG
Basic material	Brass, nickel-plated	Diameter of sealing ring	20.40 mm
Sealing	NBR	External thread	PG 13.5
Length of thread	6 mm		

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

