

**BFSC M4X35****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7 mm, Height: 35 mm
Order No.	<a href="#">0298900000</a>
Type	BFSC M4X35
GTIN (EAN)	4008190090487
Qty.	50 items

## BFSC M4X35

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	7 mm	Depth (inches)	0.2756 inch
Height	35 mm	Height (inches)	1.378 inch
Width	7 mm	Width (inches)	0.2756 inch
Diameter	4 mm	Net weight	3.16 g

## Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Steel	Colour	silver
----------------	-------	--------	--------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

## Dimensions

Diameter	4 mm	Metric size of the thread, external	4.00 mm
----------	------	-------------------------------------	---------

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		