

**BFSC M2.5X18 PA/RT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Mounting screw (Terminal), 2.50 mm, Polyamide 66, Depth: 3.8 mm, Width: 4.5 mm, Height: 18 mm
Order No.	<a href="#">0303300000</a>
Type	BFSC M2.5X18 PA/RT
GTIN (EAN)	4008 190040673
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-10T00:00:00+02:00

**BFSC M2.5X18 PA/RT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	3.8 mm	Depth (inches)	0.1496 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	4.5 mm	Width (inches)	0.1772 inch
Diameter	2.5 mm	Net weight	0.1 g

**Temperatures**

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

**System specifications**

Version for cross-connection link

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

**Dimensions**

Diameter	2.5 mm	Metric size of the thread, external	2.50 mm
----------	--------	-------------------------------------	---------

**General**

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		