

## BB 1 AKB 4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

Version	Partition plate (terminal), beige, Height: 27 mm, Width: 7 mm, V-2, PA 66
Order No.	<a href="#">0320560000</a>
Type	BB 1 AKB 4
GTIN (EAN)	4008190102555
Qty.	50 items

## BB 1 AKB 4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	23 mm	Depth (inches)	0.9055 inch
Height	27 mm	Height (inches)	1.063 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	2.34 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

### System specifications

Version	Mounting block
---------	----------------

### Additional technical data

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		