


AH 28 SAKG28

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	Terminal cover, beige, PA 66, Height: 156 mm, Width: 26 mm, Depth: 74 mm, V-2
Order No.	0326660000
Type	AH 28 SAKG28
GTIN (EAN)	4008190031510
Qty.	5 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	74 mm	Depth (inches)	2.9134 inch
Height	156 mm	Height (inches)	6.1417 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	66.8 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	Hood
---------	------

Additional technical data

Snap-on	Yes	Installation advice	Direct mounting
---------	-----	---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		