

BS 25 O.IH SAKT1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Mounting screw (Terminal), 3.00 mm, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm
Order No.	0334700000
Type	BS 25 O.IH SAKT1
GTIN (EAN)	4008190118839
Qty.	50 items

BS 25 O.IH SAKT1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	28.7 mm	Depth (inches)	1.1299 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	5.5 mm	Width (inches)	0.2165 inch
Diameter	5.5 mm	Net weight	1.7 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Brass	Colour	beige
----------------	-------	--------	-------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

Dimensions

Diameter	5.5 mm	Metric size of the thread, external	3.00 mm
----------	--------	-------------------------------------	---------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		