

**MB M6/M4 GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Sliding nut, M 6
Order No.	<a href="#">0334900000</a>
Type	MB M6/M4 GR
GTIN (EAN)	4008 190057602
Qty.	20 items

## MB M6/M4 GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	14 mm	Depth (inches)	0.5512 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	12 mm	Width (inches)	0.4724 inch
Net weight	3.45 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Polyamide 66	Surface finish	untreated
Colour	grey	UL 94 flammability rating	V-2

### System specifications

Version	For the mounting rails	Mounting rail	TS 32
---------	------------------------	---------------	-------

### Additional technical data

Type of fixing	Snap-on	Explosion-tested version	No
----------------	---------	--------------------------	----

### Dimensions

Internal thread	M 6	Pitch in mm (P)	12.00 mm
-----------------	-----	-----------------	----------

### General

Surface finish	untreated	Mounting rail	TS 32
----------------	-----------	---------------	-------

### Classifications

ETIM 8.0	EC000096	ETIM 9.0	EC000096
ETIM 10.0	EC000096	ECLASS 14.0	23-11-07-16
ECLASS 15.0	23-11-07-16		

Drawings

