

BS 25 IH/BL SAKT1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|---|
| Version | Mounting screw (Terminal), 3.00 mm, Steel, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm |
| Order No. | 0335400000 |
| Type | BS 25 IH/BL SAKT1 |
| GTIN (EAN) | 4008190086879 |
| Qty. | 50 items |

BS 25 IH/BL SAKT1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------|---------|-----------------|-------------|
| Depth | 28.7 mm | Depth (inches) | 1.1299 inch |
| Height | 5.5 mm | Height (inches) | 0.2165 inch |
| Width | 5.5 mm | Width (inches) | 0.2165 inch |
| Diameter | 3 mm | Net weight | 1.76 g |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4 |

Material data

| | | | |
|----------------|--------------|--------|------|
| Basic material | Steel, Brass | Colour | blue |
|----------------|--------------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|---------------------|-----------------|------------------|-----------------|
| Installation advice | Direct mounting | Type of mounting | when screwed in |
|---------------------|-----------------|------------------|-----------------|

Dimensions

| | | | |
|----------|------|-------------------------------------|---------|
| Diameter | 3 mm | Metric size of the thread, external | 3.00 mm |
|----------|------|-------------------------------------|---------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |