

BS 25 IH/GN SAKT1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Mounting screw (Terminal), 3.00 mm, Steel, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm
Order No.	033560000
Type	BS 25 IH/GN SAKT1
GTIN (EAN)	4008190113490
Qty.	50 items

BS 25 IH/GN SAKT1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	28.7 mm	Depth (inches)	1.1299 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	5.5 mm	Width (inches)	0.2165 inch
Diameter	3 mm	Net weight	1.78 g

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4		

Material data

Basic material Steel, Brass Colour green

System specifications

Version for cross-connection link

Additional technical data

Installation advice Direct mounting Type of mounting when screwed in

Dimensions

Diameter 3 mm Metric size of the thread, external 3.00 mm

General

Installation advice Direct mounting

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		