

**BS 25 IH/GN SAKT1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Mounting screw (Terminal), 3.00 mm, Steel, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm
Order No.	<a href="#">033560000</a>
Type	BS 25 IH/GN SAKT1
GTIN (EAN)	4008190113490
Qty.	50 items

**BS 25 IH/GN SAKT1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	28.7 mm	Depth (inches)	1.1299 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	5.5 mm	Width (inches)	0.2165 inch
Diameter	3 mm	Net weight	1.78 g

**Temperatures**

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4		

**Material data**

Basic material Steel, Brass Colour green

**System specifications**

Version for cross-connection link

**Additional technical data**

Installation advice Direct mounting Type of mounting when screwed in

**Dimensions**

Diameter 3 mm Metric size of the thread, external 3.00 mm

**General**

Installation advice Direct mounting

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		