

**BS 25 IH/VI SAKT1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Mounting screw (Terminal), 3.00 mm, Steel, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm
Order No.	<a href="#">0335800000</a>
Type	BS 25 IH/VI SAKT1
GTIN (EAN)	4008190039196
Qty.	50 items

## BS 25 IH/VI SAKT1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	28.7 mm	Depth (inches)	1.1299 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	5.5 mm	Width (inches)	0.2165 inch
Diameter	3 mm	Net weight	1.74 g

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4

### Material data

Basic material	Steel, Brass	Colour	violet
----------------	--------------	--------	--------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

### Dimensions

Diameter	3 mm	Metric size of the thread, external	3.00 mm
----------	------	-------------------------------------	---------

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		