

**BS 25 IH/VI SAKT1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

|            |                                                                                                 |
|------------|-------------------------------------------------------------------------------------------------|
| Version    | Mounting screw (Terminal), 3.00 mm, Steel, Brass, Depth: 28.7 mm, Width: 5.5 mm, Height: 5.5 mm |
| Order No.  | <a href="#">0335800000</a>                                                                      |
| Type       | BS 25 IH/VI SAKT1                                                                               |
| GTIN (EAN) | 4008190039196                                                                                   |
| Qty.       | 50 items                                                                                        |

## BS 25 IH/VI SAKT1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|          |         |                 |             |
|----------|---------|-----------------|-------------|
| Depth    | 28.7 mm | Depth (inches)  | 1.1299 inch |
| Height   | 5.5 mm  | Height (inches) | 0.2165 inch |
| Width    | 5.5 mm  | Width (inches)  | 0.2165 inch |
| Diameter | 3 mm    | Net weight      | 1.74 g      |

## Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4 |

## Material data

|                |              |        |        |
|----------------|--------------|--------|--------|
| Basic material | Steel, Brass | Colour | violet |
|----------------|--------------|--------|--------|

## System specifications

|         |                           |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

## Additional technical data

|                     |                 |                  |                 |
|---------------------|-----------------|------------------|-----------------|
| Installation advice | Direct mounting | Type of mounting | when screwed in |
|---------------------|-----------------|------------------|-----------------|

## Dimensions

|          |      |                                     |         |
|----------|------|-------------------------------------|---------|
| Diameter | 3 mm | Metric size of the thread, external | 3.00 mm |
|----------|------|-------------------------------------|---------|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |