

## Q 3 SAK4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

### General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 3, Pitch in mm (P): 6.00, Insulated: No, Width: 18 mm
Order No.	<a href="#">0336800000</a>
Type	Q 3 SAK4
GTIN (EAN)	4008190089795
Qty.	50 items

## Q 3 SAK4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	20.5 mm	Depth (inches)	0.8071 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	7.36 g		

## Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## Material data

Basic material CuSn Colour grey

## System specifications

Version for cross-connection link

## Additional technical data

Type of fixing when screwed in Installation advice Direct mounting  
Explosion-tested version No

## Dimensions

Pitch in mm (P) 6.00 mm

## General

Number of poles 3 Installation advice Direct mounting

## Rating data

Rated voltage 400 V Nominal current 32 A

## Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		