

QL 10 SAKB10



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com





The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 36 A, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 97 mm
0.1.11	
Order No.	0338400000
Туре	QL 10 SAKB10
GTIN (EAN)	4008190139452
Qty.	20 items
Delivery status	This article will no longer be available in the future.
Available until	2026-06-30T00:00:00+02:00



QL 10 SAKB10



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
ROHS	Conform		
Dimensions and weights			
D	0	D 4/: 1)	0.0707: 1
Depth	2 mm	Depth (inches)	0.0787 inch
Height Width	6 mm 97 mm	Height (inches) Width (inches)	0.2362 inch 3.8189 inch
Net weight	7.4 g	viatii (iliches)	3.0 109 111011
Temperatures	7. 7 9		
Tomporaturoo			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Environmental Product C	Compliance		
RoHS Compliance Status	Compliant without exer	mption	
REACH SVHC	No SVHC above 0.1 wt		
Material data			
Basic material	Cu Zn	Colour	grey
System specifications			
Version	Cross-connector		
Additional technical data	1		
Toma of fining	vella an a anaveral in	Installation advice	Discot secunting
Type of fixing Explosion-tested version	when screwed in No	Type of mounting	Direct mounting when screwed in
Explosion-tested version	NO	Type of mounting	when sciewed in
Dimensions			
Pitch in mm (P)	6.00 mm		
General			
Number of poles	10	Installation advice	Direct mounting
Rating data			
Nominal current	36 A		
Classifications			
ETIM 6.0	EC000489	ETIM 7.0	EC000489
TIM 8.0	EC000489	ETIM 9.0	EC000489
TIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Creation date 04.11.2025 07:30:33 MEZ

Catalogue status / Drawings 2

QL 10 SAKB10



Weidmüller Interface GmbH & Co. KG

3

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Туре	BFSC M4X9T	Version
Order No.	0103300000	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190023348	mm, Height: 9 mm
Qty.	100 ST	
Туре	SS M4 D 128-A 4	Version
Type Order No.	SS M4 D 128-A 4 0136400000	Version Lock washer, Copper