

STB 30.5 IH/SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Socket (terminal), Plug-in depth: 10 mm, Depth: 31.7 mm
Order No.	0341000000
Type	STB 30.5 IH/SW
GTIN (EAN)	4008190015299
Qty.	50 items

STB 30.5 IH/SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	31.7 mm	Depth (inches)	1.248 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Diameter	7.2 mm	Net weight	2.52 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	PA 66	Colour	black
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails
---------	------------------------

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

Dimensions

Diameter	7.2 mm	Length of thread	7 mm
Plug-in depth	10 mm		

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		