

STB 30.5 IH/RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Socket (terminal), Plug-in depth: 10 mm, Depth: 31.7 mm
Order No.	0341300000
Type	STB 30.5 IH/RT
GTIN (EAN)	4008190157852
Qty.	50 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	31.7 mm	Depth (inches)	1.248 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Net weight	2.48 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	PA 66	Colour	red
UL 94 flammability rating	V-2		

System specifications

Version For the mounting rails

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

Dimensions

Length of thread	7 mm	Plug-in depth	10 mm
------------------	------	---------------	-------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		