

**STB 30.5 IH/RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 10 mm, Depth: 31.7 mm
Order No.	<a href="#">0341300000</a>
Type	STB 30.5 IH/RT
GTIN (EAN)	4008190157852
Qty.	50 items

**STB 30.5 IH/RT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	31.7 mm	Depth (inches)	1.248 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Net weight	2.48 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

**Material data**

Basic material	PA 66	Colour	red
UL 94 flammability rating	V-2		

**System specifications**

Version For the mounting rails

**Additional technical data**

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

**Dimensions**

Length of thread	7 mm	Plug-in depth	10 mm
------------------	------	---------------	-------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		