

**STB 25 IH/BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 13 mm, Depth: 30.5 mm
Order No.	<a href="#">0343400000</a>
Type	STB 25 IH/BL
GTIN (EAN)	4008190107192
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00
Alternative product	<a href="#">STB 2.1.6/IH/BL WTL6/3</a>

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	30.5 mm	Depth (inches)	1.2008 inch
Width	7.2 mm	Width (inches)	0.2835 inch
Diameter	7.2 mm	Net weight	4.2 g

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea		

### Material data

Basic material	PA 66	Colour	blue
UL 94 flammability rating	V-2		

### System specifications

Version	For the mounting rails
---------	------------------------

### Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

### Dimensions

Diameter	7.2 mm	Plug-in depth	13 mm
----------	--------	---------------	-------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		