

KISC M3X15/6 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Clamping yoke, Mounting screw, Steel
Order No.	0359000000
Type	KISC M3X15/6 SAK2.5
GTIN (EAN)	4008190061548
Qty.	100 items

KISC M3X15/6 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	4.8 mm	Width (inches)	0.189 inch
Net weight	0.84 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Surface finish	Miscellaneous
Colour	silver		

System specifications

Version	for busbars
---------	-------------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Metric size of the thread, external	3.00 mm
-------------------------------------	---------

General

Installation advice	Direct mounting	Surface finish	Miscellaneous
---------------------	-----------------	----------------	---------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		