

H1,0/6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 6 mm, 6 mm, No
Order No.	0372600000
Type	H1,0/6
GTIN (EAN)	4008190180263
Qty.	1000 items
Packaging	loose

H1,0/6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.04 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	1.4 mm	Contact surface length (L2)	6 mm
Collar diameter (D2)	2.5 mm	L1 in mm	6.00 mm
Wire connection cross section AWG, max.	AWG 17	Stripping length	6 mm
Conductor cross-section	1 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawings

