

## H2,5/7

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

### General ordering data

Version	Wire-end ferrule, Standard, 7 mm, 7 mm, No
Order No.	<a href="#">0373000000</a>
Type	H2,5/7
GTIN (EAN)	4008190173463
Qty.	1000 items
Packaging	loose

## H2,5/7

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

### Dimensions and weights

Net weight	0.07 g
------------	--------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

### Wire-end ferrules

Contact surface diameter (D1)	2.2 mm	Contact surface length (L2)	7 mm
Collar diameter (D2)	3.4 mm	L1 in mm	7.00 mm
Wire connection cross section AWG, max.	AWG 14	Stripping length	7 mm
Conductor cross-section	2.5 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

**Drawings**

