

H10,0/18

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in poly-bag

General ordering data

Version	Wire-end ferrule, Standard, 18 mm, 18 mm, No
Order No.	0379300000
Type	H10,0/18
GTIN (EAN)	4008190156091
Qty.	500 items
Packaging	loose

H10,0/18

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.44 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	4.5 mm	Contact surface length (L2)	18 mm
Collar diameter (D2)	5.8 mm	L1 in mm	18.00 mm
Wire connection cross section AWG, max.	AWG 8	Stripping length	18 mm
Conductor cross-section	10 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawings

