

**IH 2.8 DB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	W-Series, Insulating sleeve
Order No.	<a href="#">0386060000</a>
Type	IH 2.8 DB
GTIN (EAN)	4008 1900434 14
Qty.	100 items

## IH 2.8 DB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

Depth	5.1 mm	Depth (inches)	0.2008 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	3.6 mm	Width (inches)	0.1417 inch
Net weight	0.17 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...75 °C
Operating temperature	-50 °C...	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
---------------------	-----------------	--------------------------	----

## General

Installation advice	Direct mounting
---------------------	-----------------

## UL rating data

Certificate No. (UR)	E60693
----------------------	--------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		