

## IH 4.8 DB

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

|            |                             |
|------------|-----------------------------|
| Version    | W-Series, Insulating sleeve |
| Order No.  | <a href="#">0386160000</a>  |
| Type       | IH 4.8 DB                   |
| GTIN (EAN) | 4008190141004               |
| Qty.       | 100 items                   |

## IH 4.8 DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5 mm   | Depth (inches)  | 0.1968 inch |
| Height     | 22 mm  | Height (inches) | 0.8661 inch |
| Width      | 7 mm   | Width (inches)  | 0.2756 inch |
| Net weight | 0.34 g |                 |             |

## Temperatures

|                       |                |                                  |               |
|-----------------------|----------------|----------------------------------|---------------|
| Storage temperature   | -25 °C...55 °C | Ambient temperature              | -5 °C...55 °C |
| Operating temperature | -50 °C...      | Continuous operating temp., max. | 100 °C        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Basic material            | PA 66 | Colour | dark beige |
| UL 94 flammability rating | V-2   |        |            |

## Additional technical data

|                     |                 |                          |    |
|---------------------|-----------------|--------------------------|----|
| Installation advice | Direct mounting | Explosion-tested version | No |
|---------------------|-----------------|--------------------------|----|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## UL rating data

|                      |        |
|----------------------|--------|
| Certificate No. (UR) | E60693 |
|----------------------|--------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |