

IH 6.3 WEM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	W-Series, Insulating sleeve
Order No.	0386260000
Type	IH 6.3 WEM GE
GTIN (EAN)	4008 190164256
Qty.	100 items

IH 6.3 WEM GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

Dimensions and weights

Depth	4.5 mm	Depth (inches)	0.1772 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	9 mm	Width (inches)	0.3543 inch
Net weight	0.46 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...55 °C
Operating temperature	-50 °C...	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
---------------------	-----------------	--------------------------	----

General

Installation advice	Direct mounting
---------------------	-----------------

UL rating data

Certificate No. (UR)	E60693
----------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		