

TST 10 SAKC10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Version	Mounting foot for mounting rail, black, Polyamide 66, without, Width: 9.85 mm
Order No.	0462700000
Type	TST 10 SAKC10
GTIN (EAN)	4008190124113
Qty.	20 items

TST 10 SAKC10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	50.8 mm	Depth (inches)	2 inch
Height	9.85 mm	Height (inches)	0.3878 inch
Width	9.85 mm	Width (inches)	0.3878 inch
Net weight	3.75 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	45173c19-8a33-4947-bc2b-512a20c76dcd

Material data

Basic material	Polyamide 66	Colour	black
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails
---------	------------------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Internal thread	without
-----------------	---------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC002625	ETIM 9.0	EC002625
ETIM 10.0	EC002625	ECLASS 14.0	27-18-28-07
ECLASS 15.0	27-18-28-07		