

## QL 2 SAK10


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

### General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 57 A, Number of poles: 2, Pitch in mm (P): 9.90, Insulated: No, Width: 16.9 mm
Order No.	<a href="#">0470300000</a>
Type	QL 2 SAK10
GTIN (EAN)	4008190023690
Qty.	100 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	16.9 mm	Width (inches)	0.6654 inch
Net weight	1.35 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Cu Zn	Colour	grey
----------------	-------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	9.90 mm
-----------------	---------

### General

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

### Rating data

Nominal current	57 A
-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		